


2 PCS

HÄFELE


***SALICE* 105° SOFT CLOSE HINGE**

Full Overlay - Clip On  
Fits Salice drill pattern




## Drilling Instructions


Hinge Cup (Door)




Mount Plate (Cabinet Side)




## Mounting Instructions



Cup fixed with pre-mounted spreading dowels.



Join the two points marked by an arrow.





Apply light pressure.

## Adjusting the Door



### Depth adjustment of door with SALICE mounting plates.

With the SALICE mounting plates with quick fixing system, a depth adjustment of the door from  $-0.5$  mm up to  $+2.8$  mm is possible via eccentric. It is not necessary to loosen further screws.





### Height adjustment of door with SALICE cruciform mounting plates with slot.

Height adjustment of door of  $\pm 2$  mm is possible by loosening the two fixing screws. The slots allow the mounting plates to slide in both directions. Afterwards the screws must be re-tightened.





### Lateral adjustment of door with SALICE concealed hinges.

The adjusting screw produces the lateral travel of the hinge arm from  $-1.5$  mm up to  $+4.5$  mm. This value is reduced to  $-0.5$  mm when using profile door hinges and mini hinges. The door moves with respect to the furniture side without coming apart. There are no further correcting actions required.




# HÄFELE



Cup fixed with pre-mounted spreading dowels.

## Tools Required:

- > 35mm Ø Drill Bit & Template Kit
- > 10mm Ø Drill Bit
- > 2mm Ø Drill Bit
- > Pencil
- > Power Drill
- > No 2 Pozidrive Screwdriver / Screw Bit



Salice Hinge Drilling Pattern

MADE IN ITALY



**HÄFELE AUSTRALIA PTY. LTD**  
ARTICLE # 483.02.404

8 MONTEREY RD DANDENONG VIC 3175  
730.83.637